



The **KEBBY™** Hand Decapper Setting the Standard for *Quality*

- High quality construction for durability and long life
- Consistent, dependable performance
- Quick and easy to operate
- To remove aluminum seal, just place the decapper over the seal to be removed and squeeze the handles
- Recycling facilitated by separating the aluminum from the glass
- Smooth, simple operation
- Painted, plated and coated for maximum corrosion resistance
- Less expensive than competitive models

All parts that contact the container cap are electroless nickel plated or stainless steel. The benefits of electroless nickel, which include high corrosion resistance and good lubricity, have been proven through extensive laboratory and field testing.

Textured handle surfaces provide a better grip than smooth-painted models. The powder coating used to "paint" Kebby decapper handles is durable, scratch-resistant and environmentally clean.

Our handle clip, as well as most other pins, clips and screws, are made of corrosion-resistant stainless steel.

An adjustable stop accommodates a wide range of cap thicknesses.

